



## Clamping hook, cylindrical, Type: 4



### Order data

Order number	370076 4
GTIN	4059245030859
Item class	37K

### Description

**Version:**

Entirely of hardened and tempered steel; burnished. Screw head resting on clamping hook when mounting.

**Application:**

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

**Optional extras:**

Springs and socket-head screws on request

### Technical description

H <sub>1</sub>	83 mm
Height H <sub>2</sub>	20 mm
F <sub>max.</sub>	20.2 kN
Ø D	32 mm

## Data sheet

$\varnothing D_2$	20 mm
B	20 mm
$\varnothing D_3$	12.5 mm
$\varnothing D_1$	17 mm
Type of product	Clamping hook