



Clamping hook, cylindrical, Type: 3



Order data

Order number	370075 3
GTIN	4059245030811
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished. With countersunk screw. Screw head recessed in the clamping hook.

Application:

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

Optional extras:

Springs and socket-head screws on request

Technical description

Height H_2	16 mm
$F_{max.}$	13.9 kN
H_1	66 mm
$\varnothing D_1$	14 mm

Data sheet

$\varnothing D_3$	10.5 mm
B	17 mm
$\varnothing D_2$	18 mm
$\varnothing D$	25 mm
Type of product	Clamping hook