



Clamping hook, cylindrical, Type: 2



Order data

Order number	370076 2
GTIN	4059245030835
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished. Screw head resting on clamping hook when mounting.

Application:

Screwed directly into a grid hole, no countersinking required. For space-saving clamping of workpieces. For space-saving clamping of workpieces. For installation in individual clamping devices.

Optional extras:

Springs and socket-head screws on request

Technical description

$F_{max.}$	8.8 kN
H_1	52 mm
Height H_2	12 mm
B	15 mm

Data sheet

$\varnothing D_1$	12 mm
$\varnothing D_2$	15 mm
$\varnothing D$	20 mm
$\varnothing D_3$	8.5 mm
Type of product	Clamping hook