

**EFFBE****Machine mount with height adjustment LM, maximum load capacity: 480kg****Order data**

Order number	086002 480
GTIN	4045197349422
Item class	08Y

**Description****Version:**

Anti-vibration systems for machines. The decoupling of machines and equipment, which are sensitive to vibration, improves process reliability and accuracy. The inserted elastomers damp body noise, vibration and impacts, and ensure optimum production results with reduced noise levels. All mounts are easy to fit and have levelling adjustment.

Elastomer metal machine mount in compact design with integrated levelling system using central adjustment screw.

**Application:**

For setting up machines without anchoring to the floor.

**Note:**

For higher loads and special applications further mounts are available on request. Air support pads available in the online shop under No. 086003 size SLM1 – SLM12.

**Technical description**

maximum load capacity, press brakes	450 kg
permissible static load	600 daN

maximum load capacity, lathes and surface grinding machines	220 kg
maximum levelling range (height adjustment Ni)	15 mm
maximum load capacity, milling machines	300 kg
maximum load capacity	480 kg
Thread Ø G	M10
Ø D	80 mm
Screw length S	80 mm
Height H	25 mm
Type of product	Anti-vibration machine mount