

EFFBE**Elastomer bearing plate EPA, maximum load capacity: 1500kg****Order data**

Order number	086006 1500
GTIN	4045197349484
Item class	08Y

Description**Version:**

Anti-vibration systems for machines. The decoupling of machines and equipment, which are sensitive to vibration, improves process reliability and accuracy. The inserted elastomers damp body noise, vibration and impacts, and ensure optimum production results with reduced noise levels. All mounts are easy to fit and have levelling adjustment.

Oil-resistant, non-ageing elastomer body, non-slip. Shore hardness (A) CR 80.

Application:

For setting up machines and equipment for which machine mounts and levelling pads are inappropriate. Bearing plates can be cut to size as required.

Note:

For higher loads and special applications further mounts are available on request. Air support pads available in the online shop under No. 086003 size SLM1 – SLM12.

Technical description

maximum load capacity	1500 kg
Height H	13 mm
Length A	100 mm
Width B	100 mm
Type of product	Anti-vibration machine mount

