



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 18/2Lmm



Order data

| | |
|--------------|---------------|
| Order number | 225200 18/2L |
| GTIN | 4960664648078 |
| Item class | 250 |

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

| | |
|--|----------------------|
| Indexable insert size | 10 |
| Insert screw | 229713 (8IP; 1.2 Nm) |
| suitable indexable insert | LOMU.. |
| Cutting edge Ø D _c | 18 mm |
| Overall length L _{tot} | 100 mm |
| Overhang L ₁ | 25 mm |
| maximum cutting depth a _{p max} | 10 mm |
| Shank Ø D _s h6 | 16 mm |
| Number of cutting edges Z | 2 |
| Shank type | Plain shank |
| Setting angle κ | 90° |
| Milling application | End milling |
| Milling application | Plunging |
| Through-coolant | yes |

Type of product

End / face mill

Accessories

Clamping screw

229713