



## Indexable milling cutter 90° MEW, with bore, Ø D / number of teeth Z: 50/4mm



### Order data

Order number	225210 50/4
GTIN	4960664648689
Item class	250

### Description

**Version:**  
**Cost-efficient due to 4 cutting edges.**

### Technical description

Cutting edge Ø D <sub>c</sub>	50 mm
suitable indexable insert	LOMU..
Insert screw	229714 (15IP; 3.5 Nm)
Indexable insert size	15
maximum cutting depth a <sub>p,max</sub>	15 mm
Overall length L <sub>tot</sub>	40 mm
Mounting bore Ø	22 mm
Number of cutting edges Z	4
Shank type	with bore
Setting angle κ	90 degrees

Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

---

## Accessories

Clamping screw	229714
----------------	--------