



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 25/3mm



Order data

Order number	225200 25/3
GTIN	4960664648153
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Overhang L_1	32 mm
Overall length L_{tot}	120 mm
Cutting edge Ø D_c	25 mm
Indexable insert size	10
maximum cutting depth $a_{p,max}$	10 mm
suitable indexable insert	LOMU..
Shank Ø D_s h6	25 mm
Insert screw	229713 (8IP; 1.2 Nm)
Number of cutting edges Z	3
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

Accessories

Clamping screw

229713