



## Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 32/2Lmm



### Order data

Order number	225200 32/2L
GTIN	4960664648269
Item class	250

### Description

**Version:**  
**Cost-efficient due to 4 cutting edges.**

### Technical description

Overall length $L_{tot}$	130 mm
Insert screw	229714 (15IP; 3.5 Nm)
Cutting edge $\varnothing D_c$	32 mm
Indexable insert size	15
Overhang $L_1$	32 mm
maximum cutting depth $a_{p\ max}$	15 mm
Shank $\varnothing D_s\ h6$	25 mm
suitable indexable insert	LOMU..
Number of cutting edges Z	2
Shank type	Plain shank
Setting angle $\kappa$	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

---

## Accessories

Clamping screw

229714