



Indexable milling cutter 90° MEW, with bore, Ø D / number of teeth Z: 80/6mm



Order data

Order number	225210 80/6
GTIN	4960664648702
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Cutting edge Ø D _c	80 mm
Insert screw	229714 (15IP; 3.5 Nm)
Overall length L _{tot}	50 mm
maximum cutting depth a _{p,max}	15 mm
Mounting bore Ø	27 mm
suitable indexable insert	LOMU..
Indexable insert size	15
Number of cutting edges Z	6
Shank type	with bore
Setting angle κ	90 degrees

Milling application	End milling
Milling application	Plunging
Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229714
----------------	--------