



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 40/4Lmm



Order data

Order number	225200 40/4L
GTIN	4960664648306
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

suitable indexable insert	LOMU..
Overall length L_{tot}	150 mm
Overhang L_1	50 mm
Shank $\varnothing D_s$ h6	32 mm
Cutting edge $\varnothing D_c$	40 mm
Insert screw	229714 (15IP; 3.5 Nm)
Indexable insert size	15
maximum cutting depth $a_{p,max}$	15 mm
Number of cutting edges Z	4
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

Accessories

Clamping screw

229714