



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 20/2XLmm



Order data

Order number	225200 20/2XL
GTIN	
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Indexable insert size	10
Insert screw	229713 (8IP; 1.2 Nm)
suitable indexable insert	LOMU..
Cutting edge Ø D _c	20 mm
Overall length L _{tot}	110 mm
Overhang L ₁	26 mm
maximum cutting depth a _{p max}	10 mm
Shank Ø D _s h6	16 mm
Number of cutting edges Z	2
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging
Through-coolant	yes

Type of product

End / face mill

Accessories

Clamping screw

229713