



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 32/3mm



Order data

Order number	225200 32/3
GTIN	4960664648283
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

Insert screw	229714 (15IP; 3.5 Nm)
Indexable insert size	15
Shank Ø D _s h6	32 mm
Overhang L ₁	32 mm
Overall length L _{tot}	130 mm
maximum cutting depth a _{p max}	15 mm
Cutting edge Ø D _c	32 mm
suitable indexable insert	LOMU..
Number of cutting edges Z	3
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging

Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229714
----------------	--------