



Indexable milling cutter 90° MEW, Plain shank, Ø D / number of teeth Z: 32/4mm



Order data

Order number	225200 32/4
GTIN	4960664648214
Item class	250

Description

Version:
Cost-efficient due to 4 cutting edges.

Technical description

maximum cutting depth $a_{p\max}$	10 mm
Overall length L_{tot}	130 mm
suitable indexable insert	LOMU..
Insert screw	229713 (8IP; 1.2 Nm)
Indexable insert size	10
Cutting edge $\varnothing D_c$	32 mm
Shank $\varnothing D_s$ h6	32 mm
Overhang L_1	40 mm
Number of cutting edges Z	4
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Plunging

Through-coolant	yes
Type of product	End / face mill

Accessories

Clamping screw	229713
----------------	--------