


KOMET® countersinking mill, Weldon shank, Type: M16

Order data

Order number	216660 M16
GTIN	4047109013155
Item class	24D

Description
Application:

For producing counterbores for cylinder head screws to DIN 74 sheet 2, from M8 with through coolant feed.

Technical description

Pack of insert screws	239652 8IP2 (1.3 Nm)
Shank $\varnothing D_s$ h6	25 mm
Minimum $\varnothing d_{\min}$	17 mm
maximum counterbore depth l	21 mm
for DIN cylinder head screws	M16
Counterbore $\varnothing D_1$ H13	26 mm
Indexable insert No. 216780 – 216910; No. 216950	24-010 / 110
Number of cutting edges Z	2
suitable indexable insert	WOEX
Number of indexable inserts	2
Overall length L_{tot}	100 mm
Shank type	Weldon shank
Through-coolant	yes
Type of product	Counterbores, countersinks

Accessories

Torx Plus® insert screw set 10 pieces Drive 8IP2

239652 8IP2