

**Garant**
**Forwards countersinking mill 180°, Weldon shank, Countersink Ø D: 32mm**

**Order data**

Order number	217160 32
GTIN	4045197552679
Item class	210

**Description**
**Standard:**

DIN 974-1 Reihe 1 (für Zylinderkopf-DIN-Schrauben).

**Note:**

The recommended indexable inserts have a corner radius of 0.4 mm. If indexable inserts with a different larger corner radius are used, the dimension  $\varnothing d_{\min}$  (see table) will not be achieved! Use GARANT torque screwdriver TQ No. **211750 size 3.0** with bit No. **674252 size 15IP**.

**Technical description**

Countersink $\varnothing D$	32 mm
Insert screw	219844 (15IP; 3.0 Nm)
Shank $\varnothing D_s$ h6	20 mm
Overhang $L_1$	55 mm
Minimum $\varnothing d_{\min}$	15 mm
Number of cutting edges Z	2
suitable indexable insert	260150
Overall length $L_{\text{tot}}$	138 mm
Shank type	Weldon shank
Through-coolant	yes
Tool exchange	PowerCard
Countersink angle	180 degrees

Type of product	Counterbores, countersinks
-----------------	----------------------------

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Clamping screw	219844
Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0