

Garant
Forwards countersinking mill 180°, Weldon shank, Countersink Ø D: 23mm

Order data

Order number	217160 23
GTIN	4045197552587
Item class	210

Description
Standard:

DIN 974-1 Reihe 1 (für Zylinderkopf-DIN-Schrauben).

Note:

The recommended indexable inserts have a corner radius of 0.4 mm. If indexable inserts with a different larger corner radius are used, the dimension $\varnothing d_{\min}$ (see table) will not be achieved! Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Countersink $\varnothing D$	23 mm
Shank $\varnothing D_s$ h6	16 mm
Overhang L_1	41 mm
Minimum $\varnothing d_{\min}$	12 mm
Insert screw	219795 1 (8IP; 1.2 Nm)
Number of cutting edges Z	2
suitable indexable insert	260142
Overall length L_{tot}	112 mm
Shank type	Weldon shank
Through-coolant	yes
Tool exchange	PowerCard
Countersink angle	180 degrees

Type of product	Counterbores, countersinks
-----------------	----------------------------

Accessories

Clamping screw Type 1	219795 1
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2