

**Garant**
**180° reverse countersinking mill, maximum countersink Ø D: 30mm**

**Order data**

Order number	217180 30
GTIN	4045197196941
Item class	210

**Description**
**Version:**

**With just one cutter (z = 1).**

**Note:**

Dimension e = programming dimension (information on the end face). Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

**Technical description**

Countersink Ø D	30 mm
L <sub>2</sub>	77 mm
Shank Ø D <sub>s</sub> h6	20 mm
L <sub>3</sub>	65 mm
Programming dimension e	6.05 mm
Insert screw	219795 1 (8IP; 1.2 Nm)
Number of cutting edges Z	1
Overhang L <sub>1</sub>	92 mm
Collar Ø D <sub>1</sub>	25 mm
Shank type	Whistle Notch
Minimum Ø d <sub>min</sub>	19 mm
suitable indexable insert	260142

Through-coolant	yes
Overall length L	142 mm
Tool exchange	PowerCard
Type of product	Counterbores, countersinks

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
Clamping screw Type 1	219795 1