

Garant
Circular mill, Carbide, Type: 18

Order data

Order number	217252 18
GTIN	4045197216526
Item class	21Q

Description
Note:

The actual groove depth S_{max} is calculated as follows: $(D-d_1) / 2$.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: P16

smallest hole $\varnothing D$: 14 - 22 mm

Internal $\varnothing d_1$: 9 mm

maximum cutting depth S_{max} : 6.5 mm

Overhang L_1 : 25 mm

Overall length L_{tot} : 71.5 mm

Technical description

maximum cutting depth S_{max}	6.5 mm
Overall length L_{tot}	71.5 mm
Shank type	Weldon
Internal $\varnothing d_1$	9 mm
Overhang L_1	25 mm
Shank $\varnothing D_s$ h6	12 mm
Set of insert screws	219818 (8IP; 3.8 Nm)
smallest hole $\varnothing D$	14 - 22 mm

Shank	DIN 6535 HB
for insert type	P16
Through-coolant	yes
Thread depth	21 mm
Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219818
-------------------------------	--------