

Garant
Circular mill (without insert), Steel, Type: 8

Order data

Order number	217400 8
GTIN	4045197216861
Item class	21Q

Description
Version:

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

for insert type: 04

smallest hole $\varnothing D$: 7.9 mm

Internal $\varnothing d_1$: 7.1 mm

maximum cutting depth S_{max} : 0.35 mm

Overhang L_1 : 17.2 mm

Overall length L_{tot} : 57.2 mm

Technical description

Internal $\varnothing d_1$	7.1 mm
Shank $\varnothing D_s$ h6	10 mm
smallest hole $\varnothing D$	7.9 mm
Set of insert screws	219820 (6 IP; 0.6 Nm)
Overall length L_{tot}	57.2 mm
Overhang L_1	17.2 mm
Shank type	Weldon
maximum cutting depth S_{max}	0.35 mm
for insert type	04
Material of milling tool	Steel

Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219820
-------------------------------	--------