


BDMT 070304 ER-JT, PR1210, Type: GG

Order data

Order number	227156 GG
GTIN	4960664622580
Item class	25A

Description
Note:

Standard application values for $a_e = 0.3 \times D$. Exactly 90° up to $a_p = 4$ mm.

Corner radius: 0.4 mm

Feed f_z per tooth: 0.09 – 0.16 mm

Technical description

Type	GG
Feed f_z per tooth	0.09 – 0.16 mm
Corner radius	0.4 mm
ISO code indexable insert	BDMT 070304 ER-JT
Grade	PR1210
Tool material	Carbide
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	180 m/min	K
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		