

Garant
Circular mill (without insert), Carbide, Type: 25XL

Order data

Order number	217405 25XL
GTIN	4045197216953
Item class	21Q

Description
Version:

No. 217400 sizes 8 and 11 as well as No. 217405 size 11L without internal cooling.

Tool exchange: PowerCard

Through-coolant: yes

for insert type: 01

smallest hole $\varnothing D$: 23 mm

Internal $\varnothing d_1$: 16 mm

maximum cutting depth S_{max} : 3 mm

Overall length L_{tot} : 148.58 mm

Shank $\varnothing D_s$ h6: 16 mm

Technical description

Set of insert screws	219822 (20 IP; 5.0 Nm)
Shank type	cylindrical
maximum cutting depth S_{max}	3 mm
Shank $\varnothing D_s$ h6	16 mm
Overall length L_{tot}	148.58 mm
Internal $\varnothing d_1$	16 mm
smallest hole $\varnothing D$	23 mm
for insert type	01
Through-coolant	yes
Thread depth	76.25 mm

Material of milling tool	Carbide
Tool exchange	PowerCard
Type of product	Circular mills

Accessories

Set of insert screws 10-piece	219822
-------------------------------	--------