



Cordless hammer drill / driver, Type: M18BPD4



Order data

Order number	070110 M18BPD4
GTIN	4002395004881
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

With low-maintenance 4-pole DC motor.

Advantage:

Brushless POWERSTATE™ motor.

Supplied with:

Supplied with 2 pcs. Li-ion batteries, charger, transport case (HD box) and belt clip.

Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.
The suitable Bluetooth tracking module can be found under 070103 BTT-1.

Technical description

Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	M18BPD-402X
maximum vibration to EN with hammer drill function	13 m/s ²
maximum speed 2nd speed	1800 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	38 mm
Battery capacity	4 Ah
maximum speed 1st speed	0 - 450 min ⁻¹
maximum twist drill size Ø in concrete	16 mm
maximum torque	60 Nm
maximum vibration to EN without hammer drill function	0.95 m/s ²
Packaging	Modular case (HD=Heavy Duty)
Number of rechargeable batteries contained	2
Motor design	4-pin
typical application	Strong
Weight	2.1 kg
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C