

Garant
High performance indexable thread mill, Weldon shank, Effective $\varnothing D$ / Overhang L_1 : 15,1/30mm

Order data

Order number	218050 15,1/30
GTIN	4045197447159
Item class	21R

Description
Version:

HPC thread milling cutters for reduced machining times.

Application:

For general use on **right-hand and left-hand internal and external threads**. For threads in **through holes** and **blind holes**.

Note:

Thread mill No. 218050 sizes 17/26 and 17/36 suitable for pitches up to and including 2.5 mm.
Thread mill No. 218050 sizes 30/65 suitable for pitches up to < 5.

Technical description

Overall length L_{tot}	85 mm
Insert size	24
Effective $\varnothing D$	15.1 mm
Fixing screw	219926
Shank $\varnothing D_s$	20 mm
Overhang L_1	30 mm
Number of cutting edges Z	1
Number of clamping slots	1
Shank type	Weldon shank

Application for type of drilling	Blind hole
Application for type of drilling	Through hole
Cutting direction	left-hand and right-hand
Through-coolant	yes
Type of product	thread milling cutter

Accessories

Clamping screw	219926
----------------	--------