

**Toolholder form C1 axial, right hand, Shank \varnothing d1: 20mm****Order data**

| | |
|--------------|---------------|
| Order number | 319107 20 |
| GTIN | 4067263224457 |
| Item class | 32V |

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

| | |
|-------------------|-------|
| h_6 | 30 mm |
| h_1 | 16 mm |
| l_1 | 55 mm |
| Shank width b_3 | 13 mm |
| b_2 | 27 mm |
| b_1 | 52 mm |

| | |
|----------------------------|----------------|
| h ₅ | 25 mm |
| h ₂ | 22 mm |
| Shank Ø D ₁ | 20 mm |
| Colour code for VDI shanks | VDI 20 |
| Shape | C |
| Type of product | VDI tool arbor |