

**Toolholder form C1 axial, right hand, Shank \varnothing d1: 16mm****Order data**

Order number	319107 16
GTIN	4067263224440
Item class	32V

Description**Version:**

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_5	20 mm
b_2	24 mm
h_6	22 mm
b_1	43 mm
h_2	17 mm
Shank width b_3	13 mm
Colour code for VDI shanks	VDI 16

Shank $\varnothing D_1$	16 mm
l_1	44 mm
h_1	12 mm
Shape	C
Type of product	VDI tool arbor