



## Toolholder form C1 axial, right hand, Shank $\varnothing$ d1: 50mm



### Order data

Order number	319107 50
GTIN	4067263224488
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

For face cutting in.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

$h_2$	34 mm
$b_2$	50 mm
Shank width $b_3$	26 mm
$h_5$	50 mm
$l_1$	100 mm
$h_6$	60 mm
Colour code for VDI shanks	VDI 50

b <sub>1</sub>	100 mm
h <sub>1</sub>	32 mm
Shank Ø D <sub>1</sub>	50 mm
Shape	C
Type of product	VDI tool arbor