



Toolholder form C2 axial, left-hand, Shank \varnothing d1: 30mm



Order data

Order number	319117 30
GTIN	4067263237419
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_1	20 mm
Colour code for VDI shanks	VDI 30
b_2	35 mm
h_6	38 mm
b_1	70 mm
Shank \varnothing D ₁	30 mm
Shank width b_3	17 mm

l_1	70 mm
h_2	29 mm
h_5	28 mm
Shape	C
Type of product	VDI tool arbor