

**Toolholder form C1 axial, right hand, Shank  $\varnothing$  d1: 40mm****Order data**

Order number	319107 40
GTIN	4067263224471
Item class	32V

**Description****Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

For face cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$h_2$	34 mm
Shank $\varnothing$ D <sub>1</sub>	40 mm
Shank width b <sub>3</sub>	20.5 mm
$l_1$	85 mm
b <sub>2</sub>	42.5 mm
$h_1$	25 mm

h <sub>6</sub>	48 mm
h <sub>5</sub>	32.5 mm
b <sub>1</sub>	85 mm
Colour code for VDI shanks	VDI 40
Shape	C
Type of product	VDI tool arbor