



Toolholder form C3 axial, right hand, Shank \varnothing d1: 16mm



Order data

Order number	319127 16
GTIN	4067263237457
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b_2	24 mm
h_1	12 mm
h_5	20 mm
Shank \varnothing D ₁	16 mm
b_1	43 mm
Shank width b_3	13 mm
h_6	22 mm

Colour code for VDI shanks	VDI 16
l_1	44 mm
h_2	17 mm
Shape	C
Type of product	VDI tool arbor