



## Toolholder form C3 axial, right hand, Shank $\varnothing$ d1: 40mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 319127 40     |
| GTIN         | 4067263237488 |
| Item class   | 32V           |

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

For face cutting in.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

|                           |         |
|---------------------------|---------|
| $h_1$                     | 25 mm   |
| Shank width $b_3$         | 20.5 mm |
| $h_2$                     | 34 mm   |
| $l_1$                     | 85 mm   |
| Shank $\varnothing$ $D_1$ | 40 mm   |
| $b_2$                     | 42.5 mm |
| $h_6$                     | 48 mm   |

|                            |                |
|----------------------------|----------------|
| h <sub>5</sub>             | 32.5 mm        |
| b <sub>1</sub>             | 85 mm          |
| Colour code for VDI shanks | VDI 40         |
| Shape                      | C              |
| Type of product            | VDI tool arbor |