

**Toolholder form C3 axial, right hand, Shank  $\varnothing$  d1: 30mm****Order data**

Order number	319127 30
GTIN	4067263237471
Item class	32V

**Description****Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

For face cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$b_1$	70 mm
$b_2$	35 mm
$h_5$	28 mm
Shank $\varnothing$ D <sub>1</sub>	30 mm
$l_1$	70 mm
Colour code for VDI shanks	VDI 30
$h_1$	20 mm

Shank width $b_3$	17 mm
$h_2$	29 mm
$h_6$	38 mm
Shape	C
Type of product	VDI tool arbor