



Toolholder form C3 axial, right hand, Shank \varnothing d1: 50mm



Order data

Order number	319127 50
GTIN	4067263237495
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank \varnothing D ₁	50 mm
l ₁	100 mm
b ₂	50 mm
h ₆	60 mm
h ₅	50 mm
h ₂	34 mm
b ₁	100 mm

Shank width b_3	26 mm
h_1	32 mm
Colour code for VDI shanks	VDI 50
Shape	C
Type of product	VDI tool arbor