

**Garant**

**GARANT Master eco VDI toolholder, form B2 radial left-hand, short, Shank  $\varnothing$  d1: 40mm**



## Order data

Order number	319016 40
GTIN	4067263237532
Item class	31V

## Description

### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

### Application:

Mainly for external machining.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

$h_5$	34.5 mm
$h_6$	48 mm
Shank $\varnothing$ D <sub>1</sub>	40 mm
$b_1$	85 mm
$h_1$	25 mm
$l_2$	44 mm

Colour code for VDI shanks	VDI 40
$l_1$	22 mm
$b_2$	42.5 mm
Shape	B
Type of product	VDI tool arbor