



## Toolholder form C3 axial, right hand, Shank $\varnothing$ d1: 20mm



### Order data

Order number	319127 20
GTIN	4067263237464
Item class	32V

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

For face cutting in.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

$l_1$	55 mm
$h_1$	16 mm
$h_6$	30 mm
$b_1$	52 mm
Shank width $b_3$	13 mm
$h_5$	25 mm
Colour code for VDI shanks	VDI 20

Shank $\varnothing D_1$	20 mm
$b_2$	27 mm
$h_2$	22 mm
Shape	C
Type of product	VDI tool arbor