

**Toolholder form C4 axial, left-hand, Shank \varnothing d1: 20mm****Order data**

Order number	319137 20
GTIN	4067263237617
Item class	32V

Description**Version:**

- **Case-hardened HRC 58 \pm 2.**
- **All functional faces ground.**
- **With ball spray nozzles.**

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_6	30 mm
Colour code for VDI shanks	VDI 20
l_1	55 mm
Shank \varnothing D_1	20 mm
b_1	52 mm
b_2	27 mm
h_1	16 mm

h_2	22 mm
h_5	25 mm
Shank width b_3	13 mm
Shape	C
Type of product	VDI tool arbor