



Toolholder form C4 axial, left-hand, Shank \varnothing d1: 40mm



Order data

Order number	319137 40
GTIN	4067263237631
Item class	32V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Colour code for VDI shanks	VDI 40
l_1	85 mm
b_1	85 mm
b_2	42.5 mm
Shank \varnothing D ₁	40 mm
h_6	48 mm
h_5	32.5 mm

h_1	25 mm
h_2	34 mm
Shank width b_3	25.5 mm
Shape	C
Type of product	VDI tool arbor