



## Toolholder form C4 axial, left-hand, Shank $\varnothing$ d1: 16mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 319137 16     |
| GTIN         | 4067263237600 |
| Item class   | 32V           |

### Description

#### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

#### Application:

For face cutting in.

#### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

### Technical description

|                                    |        |
|------------------------------------|--------|
| $h_1$                              | 12 mm  |
| Shank $\varnothing$ D <sub>1</sub> | 16 mm  |
| $h_6$                              | 22 mm  |
| $h_2$                              | 17 mm  |
| $b_2$                              | 24 mm  |
| Colour code for VDI shanks         | VDI 16 |
| $h_5$                              | 20 mm  |

|                   |                |
|-------------------|----------------|
| Shank width $b_3$ | 13 mm          |
| $l_1$             | 44 mm          |
| $b_1$             | 43 mm          |
| Shape             | C              |
| Type of product   | VDI tool arbor |