



Toolholder form C4 axial, left-hand, Shank \varnothing d1: 30mm



Order data

Order number	319137 30
GTIN	4067263237624
Item class	32V

Description

Version:

- Case-hardened HRC 58 ± 2 .
- All functional faces ground.
- With ball spray nozzles.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_5	28 mm
Shank width b_3	23 mm
Shank \varnothing D_1	30 mm
b_2	35 mm
h_6	38 mm
Colour code for VDI shanks	VDI 30
l_1	70 mm

h_1	20 mm
h_2	29 mm
b_1	70 mm
Shape	C
Type of product	VDI tool arbor