


**Toolholder form B4 radial left-hand, short, Shank  $\varnothing$  d1: 16mm**

**Order data**

Order number	319037 16
GTIN	4067263015376
Item class	32V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

Shank $\varnothing$ D <sub>1</sub>	16 mm
h <sub>5</sub>	20 mm
l <sub>1</sub>	13 mm
l <sub>2</sub>	24 mm
h <sub>1</sub>	12 mm

$b_2$	23 mm
$h_2$	17 mm
$h_6$	30 mm
$b_1$	42 mm
Colour code for VDI shanks	VDI 16
Shape	B
Type of product	VDI tool arbor