

**Garant**

**GARANT Master eco VDI toolholder, form B5 radial right-hand, long, Shank Ø d1: 40mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 319046 40     |
| GTIN         | 4067263237761 |
| Item class   | 31V           |

**Description**
**Version:**

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT Eco – For use with normal clamping/screw-on toolholders, GARANT Eco – system grooving toolholders No. 273830 – 273891 and GARANT Eco – parting-off toolholder No. 273651.**

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

|                            |        |
|----------------------------|--------|
| Colour code for VDI shanks | VDI 40 |
| $l_2$                      | 44 mm  |
| $h_1$                      | 25 mm  |

|                         |                |
|-------------------------|----------------|
| $b_2$                   | 75.5 mm        |
| $h_6$                   | 48 mm          |
| Shank $\varnothing D_1$ | 40 mm          |
| $l_1$                   | 22 mm          |
| $h_5$                   | 38.5 mm        |
| $b_1$                   | 118 mm         |
| Shape                   | B              |
| Type of product         | VDI tool arbor |