

Garant

GARANT Master eco VDI toolholder, form C1 axial, right hand, Shank \varnothing d1: 40mm



Order data

Order number	319106 40
GTIN	4067263237969
Item class	31V

Description

Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

h_5	32.5 mm
l_1	85 mm
b_2	42.5 mm
b_1	85 mm

Shank $\varnothing D_1$	40 mm
Colour code for VDI shanks	VDI 40
h_1	25 mm
h_6	48 mm
h_2	34 mm
Shank width b_3	20.5 mm
Shape	C
Type of product	VDI tool arbor