

Garant

GARANT Master eco VDI toolholder, form B6 radial left-hand, long, Shank \varnothing d1: 30mm



Order data

Order number	319056 30
GTIN	4067263237778
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT Eco – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	65 mm
h ₁	20 mm
l ₁	22 mm

Colour code for VDI shanks	VDI 30
Shank $\varnothing D_1$	30 mm
h_5	36 mm
l_2	40 mm
h_6	38 mm
b_1	100 mm
Shape	B
Type of product	VDI tool arbor