

Garant

GARANT Master eco VDI toolholder, form C1 axial, right hand, Shank \varnothing d1: 25mm



Order data

Order number	319106 25
GTIN	4067263237945
Item class	31V

Description

Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

b ₂	33 mm
Shank width b ₃	19 mm
h ₆	30 mm
h ₁	16 mm

Colour code for VDI shanks	VDI 25
Shank $\varnothing D_1$	25 mm
h_5	25 mm
l_1	55 mm
b_1	58 mm
Shape	C
Type of product	VDI tool arbor