

Garant
GARANT Master eco VDI toolholder, form B7 radial right-hand, long, Shank \varnothing d1: 40mm

Order data

Order number	319066 40
GTIN	4067263237907
Item class	31V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

l_2	44 mm
l_1	22 mm
Colour code for VDI shanks	VDI 40
h_5	42.5 mm
h_6	48 mm
b_2	75.5 mm

h ₁	25 mm
b ₁	118 mm
Shank Ø D ₁	40 mm
Shape	B
Type of product	VDI tool arbor