

Garant

GARANT Master eco VDI toolholder, form C2 axial, left-hand, Shank Ø d1: 30mm



Order data

Order number	319116 30
GTIN	4067263238003
Item class	31V

Description

Version:

- Case-hardened HRC 58 ± 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Colour code for VDI shanks	VDI 30
h_6	38 mm
b_1	70 mm
l_1	70 mm

h_5	28 mm
Shank $\varnothing D_1$	30 mm
b_2	35 mm
h_2	29 mm
h_1	20 mm
Shank width b_3	17 mm
Shape	C
Type of product	VDI tool arbor