

**Garant**

**GARANT Master eco VDI toolholder, form C2 axial, left-hand, Shank  $\varnothing$  d1: 40mm**



## Order data

Order number	319116 40
GTIN	4067263238010
Item class	31V

## Description

### Version:

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.**

### Application:

For face cutting in.

### Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

## Technical description

b <sub>2</sub>	42.5 mm
h <sub>2</sub>	34 mm
h <sub>5</sub>	32.5 mm
l <sub>1</sub>	85 mm

Colour code for VDI shanks	VDI 40
$b_1$	85 mm
$h_1$	25 mm
Shank $\varnothing D_1$	40 mm
Shank width $b_3$	20.5 mm
$h_6$	48 mm
Shape	C
Type of product	VDI tool arbor