

**Garant**
**GARANT Master eco VDI toolholder, form C3 axial, right hand, Shank  $\varnothing$  d1: 40mm**

**Order data**

Order number	319126 40
GTIN	4067263238065
Item class	31V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT Eco** – For use with normal clamping/screw-on toolholders, **GARANT Eco** – system grooving toolholders No. 273830 – 273891 and **GARANT Eco** – parting-off toolholder No. 273651.

**Application:**

For face cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

$b_1$	85 mm
$h_1$	25 mm
$l_1$	85 mm
$b_2$	42.5 mm

Colour code for VDI shanks	VDI 40
$h_2$	34 mm
Shank width $b_3$	20.5 mm
Shank $\varnothing D_1$	40 mm
$h_5$	32.5 mm
$h_6$	48 mm
Shape	C
Type of product	VDI tool arbor