

Garant

GARANT Master eco VDI toolholder, form C3 axial, right hand, Shank \varnothing d1: 50mm


Order data

Order number	319126 50
GTIN	4067263238072
Item class	31V

Description
Version:

- Case-hardened HRC 58 \pm 2.
- All functional faces ground.
- With ball spray nozzles.

GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.

Application:

For face cutting in.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Shank \varnothing D ₁	50 mm
b ₂	50 mm
h ₆	60 mm
h ₁	25 mm

Colour code for VDI shanks	VDI 50
h_2	41 mm
h_5	50 mm
b_1	100 mm
l_1	100 mm
Shank width b_3	26 mm
Shape	C
Type of product	VDI tool arbor