

**Garant**
**GARANT Master eco VDI toolholder, form C4 axial, left-hand, Shank  $\varnothing$  d1: 40mm**

**Order data**

Order number	319136 40
GTIN	4067263238119
Item class	31V

**Description**
**Version:**

- Case-hardened HRC 58  $\pm$  2.
- All functional faces ground.
- With ball spray nozzles.

**GARANT eco – For use with normal clamping toolholders, with GARANT eco – system grooving toolholders No. 273830 – 273891 and with GARANT eco – parting-off toolholders No. 273651.**

**Application:**

For face cutting in.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

**Technical description**

Shank $\varnothing$ D <sub>1</sub>	40 mm
b <sub>2</sub>	42.5 mm
h <sub>6</sub>	48 mm
b <sub>1</sub>	85 mm

Shank width $b_3$	20.5 mm
$h_5$	32.5 mm
Colour code for VDI shanks	VDI 40
$h_1$	25 mm
$h_2$	34 mm
$l_1$	85 mm
Shape	C
Type of product	VDI tool arbor